

# Hub City™ Farm Products And Accessories

## Warranty

The proper selection and application of power transmission products and components, including the related area of product safety, is the responsibility of the customer. Operating and performance requirements and potential associated issues will vary appreciably depending upon the use and application of such products and components. The scope of the technical and application information included in this publication is necessarily limited. Unusual operating environments and conditions, lubrication requirements, loading supports, and other factors can materially affect the application and operating results of the products and components and the customer should carefully review its requirements. Any technical advice or review furnished by Regal Beloit America, Inc. and/or its

affiliates ("Regal") with respect to the use of products and components is given in good faith and without charge, and Regal assumes no obligation or liability for the advice given, or results obtained, all such advice and review being given and accepted at customer's risk. For a copy of our Standard Terms and Conditions of Sale, please visit <http://www.regalbeloit.com> (please see link at bottom of page to "Standard Terms and Conditions of Sale"). These terms and conditions of sale, disclaimers and limitations of liability apply to any person who may buy, acquire or use a Regal product referred to herein, including any person who buys from a licensed distributor of these branded products.

## Adjustment Policy

SPLINED SHAFT ADAPTORS: Broken or damaged splined shaft adaptors returned directly to the factory in Aberdeen, South Dakota, will be replaced on a no-charge basis.

FOR USER/OPERATOR SAFETY, SEE DETAILS ON PAGES L-4, L-5 & L-11

## How To Order

When ordering Hub City farm products and accessories specify the part number and quantity for each item ordered. Orders may be placed by mail, telephone, fax or e-mail.

Hub City, Inc.  
Box 1089  
Aberdeen, SD 57402-1089

Telephone: 605/225-0360 Fax: 605/225-0567  
E-Mail: [hubsales@regalbeloit.com](mailto:hubsales@regalbeloit.com)  
Website: [www.regalbeloit.com](http://www.regalbeloit.com)

**⚠ DANGER**

FOR USER/OPERATOR SAFETY  
SEE DETAILS PAGE L-11

# Hub City™ Farm Products And Accessories

## Non P.T.O. Products

### Non P.T.O. Product Safety

**⚠ DANGER**

For safety, purchaser or user must provide protective guards over all rotating shafts and any moving apparatus mounted thereon. The user is responsible for checking all applicable safety codes in the relevant area and for the equipment utilizing this component, and providing suitable guards.

Buyer shall be solely responsible for determining the adequacy of this product for any and all uses to which the buyer shall apply this product. The application by the buyer shall not be subject to any implied warranty of fitness for a particular purpose. The purchaser/user of this component accepts responsibility for the above issues when removing the safety warning label from the component.

**⚠ DANGER**

DO NOT OPERATE WITHOUT PROPER GUARDS. FAILURE TO GUARD CAN RESULT IN SERIOUS INJURY OR DEATH AND DAMAGE TO THE EQUIPMENT.



**⚠ DANGER**FOR USER/OPERATOR SAFETY  
SEE DETAILS PAGE L-11**Hub City™ Farm Products And Accessories****Non P.T.O. Products****Splined Shafts**

SIZE	SPLINE	LENGTH (INCHES)	PART NUMBER
1	6	10	0332-00390
1 1/8	6	10	0332-00391
1 1/4	6	10	0332-00392
1 1/4	10	10	0332-00393
1 3/8	6	10	0332-00394
1 1/2	6	10	0332-00396
1 5/8	6	10	0332-00397
1 3/4	6	10	0332-00398

**Extension Shafts**

SIZE	SPLINE	LENGTH (INCHES)	PART NUMBER
1 3/8-6	1 3/8-6	9	0332-00356
1 3/8-6	1 1/8-6	9	0332-00357

**Involute Splined Shafts**

NO. OF SPLINES	SPLINE DESCRIPTION	SPLINE O.D.	SHAFT LENGTH	PART NUMBER
9	16/32 DP 30° PA	.625	6	0332-00023
13	16/32 DP 30° PA	.875	6	0332-00024
15	16/32 DP 30° PA	1	8	0332-00044
14	12/24 DP 30° PA	1.25	10	0332-00025
21	16/32 DP 30° PA	1.375	10	0332-00395
16	10/20 DP 30° PA	1.7	10	0332-00038
13	8/16 DP 30° PA	1.75	10	0332-00026
27	16/32 DP 30° PA	1.75	10	0332-00399
34	20/40 DP 30° PA	1.750	10	0332-00415*
16	8/16 DP 30° PA	2.125	10	0332-00039



\* Manufactured to order